Product datasheet

Specification





Spacial S3D plain door w/o mount.plate. H1000xW1000xD300 IP66 IK10 RAL7035.

Local distributor code: 392867168

NSYS3D101030

EAN Code: 3606480160349

Main

| Range | Spacial |
|-----------------------------|--|
| Product Name | Spacial S3D |
| Application | Multi-purpose |
| Category | Compact enclosure |
| Enclosure Nominal Height | 1000 mm |
| Enclosure Nominal Width | 1000 mm |
| Enclosure Nominal Depth | 300 mm |
| Door Type | Plain |
| Mounting Plate Description | Without mounting plate |
| Type Of Gland Plate | Standard |
| Installation Accessory Type | Wall-mounting |
| Device Composition | 1 body 2 cable gland plate 1 door 1 lock |

Complementary

| Body Type | Single piece body |
|-----------------------------|---|
| | Gutter-shaped front rail double sheet thickness |
| Number Of Doors | Front face: 1 door(s) |
| Door Opening Side | Reversible (120 °) |
| Lock Type | 3 points lock, 3 mm double-bar |
| Accessibility For Operation | Front |
| Removable Parts | Door by hinges |
| | Cable gland plate by screws |
| Material | Steel |
| Surface Finish | Epoxy-polyester powder |
| Colour | Grey (RAL 7035) |
| Standards | IEC 62208 |
| Product Certifications | LR |
| | BV |
| | UL |
| | GL |
| | DNV |
| | cUL |
| Net Weight | 46 kg |

Environment

| Nema Degree Of Protection | NEMA 4X/13 |
|---------------------------|------------------------------|
| Ik Degree Of Protection | IK10 conforming to IEC 62262 |
| Ip Degree Of Protection | IP66 conforming to IEC 60529 |

Packing Units

| r adming dimes | |
|------------------------------|----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 35 cm |
| Package 1 Width | 102 cm |
| Package 1 Length | 103 cm |
| Package 1 Weight | 43.6 kg |
| Unit Type Of Package 2 | PAL |
| Number Of Units In Package 2 | 3 |
| Package 2 Height | 115 cm |
| Package 2 Width | 102 cm |
| Package 2 Length | 120 cm |
| Package 2 Weight | 142.6 kg |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |