# **Product datasheet**

Specification





# Spacial S3D plain door w/o mount.plate. H1000xW1200xD400 IP55 IK10 RAL7035.

Local distributor code: 392867249

NSYS3D101240D

EAN Code: 3606480160264

#### Main

Range	Spacial
Product Name	Spacial S3D
Application	Multi-purpose
Category	Compact enclosure
Enclosure Nominal Height	1000 mm
Enclosure Nominal Width	1200 mm
Enclosure Nominal Depth	400 mm
Door Type	Plain
Mounting Plate Description	Without mounting plate
Type Of Gland Plate	Standard
Installation Accessory Type	Wall-mounting
<b>Device Composition</b>	1 body 2 cable gland plate 1 lock 2 door

### Complementary

-	
Body Type	Gutter-shaped front rail double sheet thickness Single piece body
Number Of Doors	Front face: 2 door(s)
Door Opening Side	Reversible (120 °)
Lock Type	3 points lock, 3 mm double-bar
Accessibility For Operation	Front
Removable Parts	Door by hinges Cable gland plate by screws
Material	Steel
Surface Finish	Epoxy-polyester powder
Colour	Grey (RAL 7035)
Standards	IEC 62208
Product Certifications	cUL UL DNV BV GL LR
Net Weight	68 kg

### **Environment**

Electromagnetic Compatibility	Electromagnetic field immunity test
Ik Degree Of Protection	IK10 conforming to IEC 62262
Ip Degree Of Protection	IP55 conforming to IEC 60529

## **Packing Units**

r adming dimes	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	46 cm
Package 1 Width	101 cm
Package 1 Length	123 cm
Package 1 Weight	68 kg
Unit Type Of Package 2	PAL
Number Of Units In Package 2	2
Package 2 Height	116 cm
Package 2 Width	100 cm
Package 2 Length	123 cm
Package 2 Weight	159 kg

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations