

Product datasheet

Specifications



Spacial SF enclosure with mounting plate - assembled - 1800x1000x400 mm

Local distributor code: 22146065 NSYSF181040P

Main

Range	Spacial
Extended range	Spacial SF
Application	Multi-purpose
Product or component type	Suitable enclosure
Enclosure nominal height	1800 mm
Enclosure nominal width	1000 mm
Enclosure nominal depth	400 mm
Enclosure mounting	Floor-standing
Device composition	2 sliding rails 4 mounting plate bracket 1 structure 1 door 1 locking system with handle: door 1 rear panel 1 roof 1 mounting plate

Complementary

Structure type	Perforated structure with a pitch of 25 mm Vertical uprights joined with top and bottom frames Panels and doors built into the structure Formed from a single section
Door type	Plain front
Number of doors	Front: 1 door(s)
Door opening side	Reversible (120 °)
Lock type	4 points lock, handle with 5 mm double bar insert front door
Mounting plate description	Plain
Type of gland plate	Without gland plate
Accessibility for operation	Rear Sides of enclosure Front
Removable parts	Door by screws hinge Mounting plate by screws mounting plate bracket Rear panel by screws Roof by screws Mounting plate bracket by screws Sliding rail by screws
Material	Frame: galvanised steel Uprights: galvanised steel Door: sheet steel

Panels: sheet steel
Hinge: zamak
Handle: polyamide 6 with 30 % fibre glass

Surface finish Epoxy-polyester powder

Colour Enclosure: grey (RAL 7035)
Handle: black (RAL 9005)

Net weight 147.462 kg

Environment

Standards IEC 62208

NEMA degree of protection NEMA 3R/12

IP degree of protection IP55 conforming to IEC 60529

IK degree of protection IK10 conforming to IEC 62262

Packing Units

Unit Type of Package 1 PCE

Number of Units in Package 1 1

Package 1 Weight 146.384 kg

Package 1 Height 193 cm

Package 1 width 104 cm

Package 1 Length 48.5 cm

Offer Sustainability

Sustainable offer status Green Premium product

REACH Regulation [REACH Declaration](#)

REACH free of SVHC Yes

EU RoHS Directive Pro-active compliance (Product out of EU RoHS legal scope)
[EU RoHS Declaration](#)

Mercury free Yes

RoHS exemption information [Yes](#)

China RoHS Regulation [China RoHS declaration](#)
Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure [Product Environmental Profile](#)

Contractual warranty

Warranty 18 months
