# **Product datasheet**

Specifications





# Spacial SFHD outdoor heavy duty - suitable enclosure - H1281 W600 D630 - IP55

Local distributor code:

402658050 NSYSFHD12660

EAN Code: 3606480676208

#### Main

Mani		
Range	Spacial	
Product	Spacial SFHD	
Specific Application	Outdoor heavy duty	
Certification	Bureau Veritas conforming to IEC 61969-3 2011 UL conforming to UL 508 A 2007 Bureau Veritas conforming to IEC 61439-5 2010 DEKRA conforming to IEC 62208 2011 Bureau Veritas conforming to ISO 12944 2007	
Device Application	Multi-purpose	
Product Or Component Type	Suitable enclosure	
Enclosure Height With Canopy	1281 mm	
Canopy Height	81 mm	
Enclosure Nominal Width	600 mm	
Enclosure Depth With Canopy	630 mm	
Enclosure Depth	600 mm	
Installation Accessory Type	Floor-standing	
Available Functions With Accessories	Suitable for electronic 19" rack Roof management Coupling Floor management	
Device Composition	sliding rails 2 mounting plate mounting plate bracket 4 structure 1 locking system with handle and padlock 1 canopy 1 mechanical retainer 1 door roof 1 door 1 Plastic document pocket 1 A4 Aluminium cable gland plate 1	

## Complementary

Structure Type	Panels and doors built into the structure Formed from a single section Perforated structure with a pitch of 25 mm Vertical uprights screwed with top and bottom frames	
Door Type	Plain	
Number Of Doors	1 door(s)	
Door Opening Side	Reversible (120 °)	
Lock Type	4 points lock, handle with 1242E key lock and padlock front door	
Mounting Plate Description	Without mounting plate	_

Cable Gland Plate Type	Plain aluminium
Accessibility For Operation	Bottom
	Sides of enclosure
	Rear
	Тор
	Front
Maximum Lifting Load	1000 kg
Removable Parts	Mounting plate bracket by screws
	Sliding rail by screws
	Rear panel by screws external part
	Roof by screws
	Canopy by screws and claws
	Door by removable axis hinge
	Cable gland plate fixing nut
Material	Frame: steel with anti-corrosive coating
	Hinge: zamak
Surface Finished Painted	On enclosure: polyester powder
Colour	Enclosure: grey (RAL 7035)
	Handle: grey (RAL 7035)
Specific Order Possible For Special Colour	Yes

## **Environment**

Standards	IEC 62208 UL 508 A IEC 61439-5 IEC 61969-3
Ip Degree Of Protection	IP55 conforming to IEC 60529
Ik Degree Of Protection	IK10 conforming to IEC 62262
Climatic Withstand	C4H conforming to ISO 12944 720 h salt mist
Ambient Air Temperature For Operation	-4580 °C conforming to IEC 61969-3 class 1
Corrosion Withstand	90100 % conforming to ISO 12944 C4H
Environmental Withstand	Solar radiation: class 1 up to 1120 W/m² conforming to IEC 61969-3:2011 Surrounding air withstand: class 1 up to 180 km/h conforming to IEC 61969-3:2011 Ultraviolet degradation test: class 1 conforming to ISO 4892-2:2013 Formation of ice and frost: class 1 conforming to IEC 61969-3:2011 Fauna and flora withstand: class 1 conforming to IEC 61969-3:2011 : class 1 conforming to IEC 61969-3:2011
Thermal Management	Fan: 1500 W for a maximum noise level of 60 dB With external cooling 4000 W Natural: 595 W at 20 °C Natural: 595 W at 40 °C According to cooling architecture 1500 W

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	65 cm
Package 1 Width	69 cm
Package 1 Length	143 cm
Package 1 Weight	79 kg

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations