Product datasheet

Specifications





PC box IP66 IK08 RAL7035 Int.H175W150D100 Ext.H193W164D105 opaque PC cover H40

Local distributor code: 387531768

NSYTBP191610H

EAN Code: 3606480165672

Main

Range	Thalassa
Product Name	Thalassa TBP
Device Application	Multi-purpose
Category	Industrial box
Height	192 mm
Width	164 mm
Depth	105 mm
Internal Height	175 mm
Internal Width	150 mm
Internal Depth	100 mm
Enclosure Mounting	Wall mounted
Device Composition	1 body 1 cover 4 cover screw
Body Type	One piece moulded
Type Of Front Cover	High plain cover
Cover Fixing	Plastic screws
Lock Type	Captive screw flat outside sealed area
Removable Parts	Cover by captive screws

Complementary

Material	Polycarbonate	
Colour	Grey (RAL 7035)	
Standards	UL 508 A IEC 62208	
Product Certifications	TÜV UL	
Electrical Insulation Class	Class II	
Mounting Location	Outdoor (with canopy or shelter and anticondensation valve)	
Net Weight	0.62 kg	

Environment

Ip Degree Of Protection IP66 conforming to NEMA 4.4X

Ik Degree Of Protection	IK08 conforming to IEC 62262
Fire Resistance	960 °C
Ambient Air Temperature For Storage	-1560 °C
Operating Temperature	-2580 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12.45 cm
Package 1 Width	17.02 cm
Package 1 Length	21.08 cm
Package 1 Weight	1.24 kg
Unit Type Of Package 2	CAR
Number Of Units In Package 2	17
Package 2 Height	40 cm
Package 2 Width	41 cm
Package 2 Length	61 cm
Package 2 Weight	10.94 kg
Unit Type Of Package 3	PAM
Number Of Units In Package 3	425
Package 3 Height	215 cm
Package 3 Width	100 cm
Package 3 Length	120 cm
Package 3 Weight	287 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
9	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information