

Product datasheet

Specifications



LoadCentre KQ - type B split metered distribution board - 125A - 12 + 8 TP ways

SEB36S24125

EAN Code: 5018934961712

Main

Range	Acti9
Product Name	Load centre KQ II B
Product Or Component Type	Distribution board
Device Application	Distribution
Enclosure Type	Split meter
Door Type	Overall
Provided Equipment	Enclosure Door Front cover Switch disconnecter - 125 A as incomer Multi-function meter - 2 nos. Shielded neutral bar 25 mm ² Earth terminal block 25 mm ² Pan assembly
Colour	Grey (RAL 7035)

Complementary

Enclosure Mounting	Surface
[Ie] Rated Operational Current	125 A at 400/415 V AC
Protection Device Options	Miniature circuit breaker (MCB) (plug-on type) as outgoer Residual current circuit breaker with overcurrent protection (RCBO) (plug-on type) as outgoer
Number Of Ways	12 ways (3P)outgoer for section 1 8 ways (3P)outgoer for section 2
Cable Entry	top and bottom: knock-out side: knock-out
Height	1290 mm
Width	470 mm
Depth	139 mm

Environment

Ip Degree Of Protection	IP2x B internal conforming to BS EN 60529 IP3x external conforming to BS EN 60529
-------------------------	--

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	15.0 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	54.0 cm
Package 1 Length	134.0 cm
Package 1 Weight	27.65 kg
Unit Type Of Package 2	PAL
Number Of Units In Package 2	12
Package 2 Height	105.0 cm
Package 2 Width	107.0 cm
Package 2 Length	150.0 cm
Package 2 Weight	341.8 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance



Mercury Free



Rohs Exemption Information

[Yes](#)

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

China Rohs Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information