



round pilot light Ø16 - IP65 orange - integral LED 24VDCpolarised - connector

Local distributor code: 395512876

XB6EAV8BP

! Discontinued on: 15 Jun 2023

! Discontinued

EAN Code: 3389110624779

Main

Range Of Product	Harmony XB6E
Product Or Component Type	Monolithic pilot light
Device Short Name	XB6E
Bezel Material	Plastic
Mounting Diameter	16 mm
Sale Per Indivisible Quantity	5
Shape Of Signaling Unit Head	Round
Cap/Operator Or Lens Colour	Orange
Light Source	Integral LED
Light Block Supply	Direct
[Us] Rated Supply Voltage	24 V DC polarised

Complementary

,	
Net Weight	0.006 kg
Overvoltage Category	II conforming to IEC 60536
Operating Position	Any position
Marking	CE
Connections - Terminals	Insulated faston, connection size: 2.8 x 0.5 mm Solder terminal, clamping capacity: <= 0.75 mm² AWG 19 Fast connector socket
Tightening Torque	0.61 N.m
[Ui] Rated Insulation Voltage	250 V (pollution degree 3) conforming to IEC 60947-1
[Uimp] Rated Impulse Withstand Voltage	2.5 kV conforming to IEC 60947-1
Signalling Type	Steady
Current Consumption	10 mA
Service Life	30000 h

Environment

Ambient Air Temperature For Storage	-4070 °C
Ambient Air Temperature For Operation	-1055 °C
Ip Degree Of Protection	IP65 conforming to IFC 60529

Standards	JIS C8201-5-1 JIS C 852 UL 508 IEC 60947-5-1 IEC 60947-1 CSA C22.2 No 14 JIS C8201-1	
Product Certifications	CCC cURus	
Vibration Resistance	1 mm (f= 1055 Hz) conforming to IEC 60068-2-6	_
Shock Resistance	10 gn (duration = 11 ms) for half sine wave acceleration conforming to IEC 60068-2-27	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.2 cm
Package 1 Width	2.8 cm
Package 1 Length	18.7 cm
Package 1 Weight	9.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	5
Package 2 Height	7.2 cm
Package 2 Width	2.8 cm
Package 2 Length	18.7 cm
Package 2 Weight	45.0 g
Unit Type Of Package 3	S01
Number Of Units In Package 3	50
Package 3 Height	15.0 cm
Package 3 Width	15.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	675.0 g

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

✓ Reach Free Of Svhc
 ✓ Mercury Free
 ✓ Rohs Exemption Information

Certifications & Standards


Circularity Profile	End of Life Information
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Environmental Disclosure	Product Environmental Profile
China Rohs Regulation	China RoHS declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Reach Regulation	REACh Declaration

XB6EAV8BP

Dimensions Drawings

Pilot Light

Circular Head



- (1) Anti-rotation plate (thickness: 0.6 mm / 0.02 in.)
- (2) Seal (thickness: 0.5 mm / 0.01 in.)
- e panel thickness: 0.5 mm (0.01 in.) \leq e \leq 6 mm (0.24 in.)

Product datasheet

XB6EAV8BP

Mounting and Clearance

Panel Cut-Out and Mounting

Circular or Square Head

