Product datasheet

Specifications





(!) Discontinued

INDICATING BEACON 230VAC 10W +OPTIONS

Local distributor code: 388813948

XVBL4M8

() Discontinued on: 9 Feb 2023

EAN Code: 3389110844290

Main

| Range Of Product | Harmony XVB Universal |
|---------------------------------------|--|
| Product Or Component Type | Complete beacon |
| Beacon Or Indicator Bank Unit Type | Base unit direct or tube fixing Illuminated unit |
| Signalling Type | Flashing |
| Mounting Diameter | 70 mm |
| Component Name | XVBL |
| Material | Glass reinforced polyamide: base unit Polycarbonate: illuminated unit |
| Light Source | Bulb not included, yellow |
| Bulb Type | Incandescent with BA 15d base Protected LED |
| [Us] Rated Supply Voltage | 48230 V AC |
| Maximum Power Dissipation In W | 7 W |

.

Complementary

| Connections - Terminals | Screw clamp terminals, <= 1 x 1.5 mm ² with cable end |
|---|--|
| [Ui] Rated Insulation Voltage | 250 V conforming to IEC 60947-1 |
| Nominal Voltage Limit | 0.851.1 Un conforming to IEC 60947-5-1 |
| [Uimp] Rated Impulse Withstand Voltage | 4 kV conforming to IEC 60947-1 |
| Flashing Frequency | 1 Hz |
| Cad Overall Width | 70 mm |
| Cad Overall Height | 139 mm |
| Cad Overall Depth | 70 mm |
| Terminals Description Iso N°1 | (COM-1)PW (GND)GROUND |
| Net Weight | 0.28 kg |

Environment

| Pollution Degree | 2 |
|------------------------|---|
| Product Certifications | CCC EAC CSA C22-2 No 14 UL 508 |

| Standards | IEC 60947-5-1 |
|--|--|
| Protective Treatment | тс |
| Ambient Air Temperature For Storage | -4070 °C |
| Electrical Shock Protection Class | Class I on support tube conforming to IEC 61140 Class II on base unit conforming to IEC 61140 |
| Ip Degree Of Protection | IP65 on fixing base XVBZ0. conforming to IEC 60529 IP66 on base unit conforming to IEC 60529 |
| Nema Degree Of Protection | Type 4X conforming to UL (indoor) |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|----------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 14.5 cm |
| Package 1 Width | 8 cm |
| Package 1 Length | 8 cm |
| Package 1 Weight | 280 g |
| Unit Type Of Package 2 | S02 |
| Number Of Units In Package 2 | 5 |
| Package 2 Height | 15 cm |
| Package 2 Width | 30 cm |
| Package 2 Length | 40 cm |
| Package 2 Weight | 1.855 kg |

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information
Yes


Certifications & Standards

| Circularity Profile | No need of specific recycling operations |
|--------------------------|---|
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Environmental Disclosure | Product Environmental Profile |
| China Rohs Regulation | China RoHS declaration |
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| Reach Regulation | REACh Declaration |

Dimensions Drawings

Illuminated Beacon for BA 15d Bulb or LED

Dimensions



Product datasheet

Connections and Schema

Illuminated Beacon

Wiring Diagram

