



LED pilot light with black bezel, Harmony XVL, Ø 8, IP40, red, protruding included, 12 V, faston

XVLA124

! Discontinued on: 9 Feb 2023

! Discontinued

EAN Code: 3389110651027

Main

Range Of Product	Harmony XVL			
Product Or Component Type LED pilot light with black bezel				
Component Name	XVL			
Mounting Diameter	8 mm			
Light Source	Protruding LED			
Light Block Colour	Red			
Protection Type	Built-in by diode Integral ballast resistor			
[Us] Rated Supply Voltage	12 V			
Ip Degree Of Protection	IP40 conforming to IEC 60529 IP40 conforming to NF C 20-010			

Complementary

Supply Circuit Type	DC
Connections - Terminals	Tag for Faston connectors: 2.8 x 0.5 mm Tag for soldering connectors
Current Consumption	18 mA
[Ui] Rated Insulation Voltage	50 V conforming to IEC 60947-1
Bulb Lifespan	100000 h
Nominal Voltage Limit	0.81.1 Un
Terminals Description Iso N°1	(X1-X2)PL
Height	12 mm
Width	12 mm
Depth	34 mm
Net Weight	0.003 kg

Environment

Product Certifications	UL CSA
Protective Treatment	TC
Ambient Air Temperature For Operation	-2570 °C
Ambient Air Temperature For Storage	-4070 °C

Overvoltage Category	Class 3 conforming to IEC 60536	
	Class 3 conforming to NF C 20-030	

Packing Units

r doming office	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.0 cm
Package 1 Width	1.0 cm
Package 1 Length	4.0 cm
Package 1 Weight	3.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	3.0 cm
Package 2 Width	13.0 cm
Package 2 Length	13.0 cm
Package 2 Weight	31.0 g
Unit Type Of Package 3	S01
Number Of Units In Package 3	100
Package 3 Height	15.0 cm
Package 3 Width	15.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	532.0 g

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards


Reach Regulation	REACh Declaration		
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)		
China Rohs Regulation	China RoHS declaration		
Environmental Disclosure	Product Environmental Profile		
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins		
Circularity Profile	No need of specific recycling operations		

XVLA124

Dimensions Drawings

LED Pilot Light

Dimensions



- (1) Tags for Faston connectors or soldered connections
- e panel thickness: 1 to 8 mm/0.03 to 0.31 in.


С		Ø	
mm	in.	mm in.	
32	1.26	12	0.47

XVLA124

Mounting and Clearance

LED Pilot Light

Panel Drilling



Ø mi	Ø min		G min		H min	
mm	in.	mm	in.	mm	in.	
8.2	0.32	12.5	0.49	12.5	0.49	