Product datasheet

Specifications





pilot light Ø8 - IP40 - green protruding LED included - 48V faston

Local distributor code: 389968368

XVLA143

EAN Code: 3389110651126

Main

Range Of Product	Harmony XVL De LED pilot light with black bezel		
Product Or Component Type			
Component Name	XVL		
Mounting Diameter	8 mm		
Light Source	Protruding LED		
Light Block Colour	Green		
Protection Type	Built-in by diode Integral ballast resistor		
[Us] Rated Supply Voltage	48 V		
Ip Degree Of Protection	IP40 conforming to IEC 60529 IP40 conforming to NF C 20-010		

Complementary

Supply Circuit Type	DC		
Connections - Terminals	Tag for Faston connectors: 2.8 x 0.5 mm Tag for soldering connectors		
Current Consumption	10 mA		
[Ui] Rated Insulation Voltage	50 V conforming to IEC 60947-1		
Bulb Lifespan	100000 h		
Nominal Voltage Limit	0.81.1 Un		
Terminals Description Iso N°1	(X1-X2)PL		
Height	12 mm		
Width	12 mm		
Depth	34 mm		
Net Weight	0.003 kg		

Environment

Product Certifications	CSA UL
Protective Treatment	тс
Ambient Air Temperature For Operation	-2570 °C
Ambient Air Temperature For Storage	-4070 °C
Overvoltage Category	Class 3 conforming to IEC 60536 Class 3 conforming to NF C 20-030

Packing Units

O	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.600 cm
Package 1 Width	4.100 cm
Package 1 Length	6.500 cm
Package 1 Weight	3.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	3.000 cm
Package 2 Width	10.000 cm
Package 2 Length	13.000 cm
Package 2 Weight	31.000 g
Unit Type Of Package 3	S01
Number Of Units In Package 3	100
Package 3 Height	15.000 cm
Package 3 Width	15.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	523.000 g

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards


Circularity Profile	No need of specific recycling operations		
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins		
Environmental Disclosure	Product Environmental Profile		
China Rohs Regulation	China RoHS declaration		
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)		
Reach Regulation	REACh Declaration		

Product datasheet

Dimensions Drawings

LED Pilot Light

Dimensions



- (1) Tags for Faston connectors or soldered connections
- e panel thickness: 1 to 8 mm/0.03 to 0.31 in.


С		Ø	
mm in.		mm	in.
32	1.26	12	0.47

Product datasheet

Mounting and Clearance

LED Pilot Light

Panel Drilling



Ø min		G min		H min	
mm	in.	mm	in.	mm	in.
8.2	0.32	12.5	0.49	12.5	0.49