

Product datasheet

Specifications



Harmony eXLhoist, Remote control
eXLhoist compact, 6 motion push
buttons, 2 auxiliary push buttons,
LED

ZART8LS

EAN Code: 3606481389107

Main

Range Of Product	Harmony eXLhoist
Product Or Component Type	Hand-held remote control
Device Short Name	ZART
Control Button Type	6 configurable motion push-button 2 configurable auxiliary push-button

Complementary

Material	Protective cover: EPDM rubber Push-button cover: polyurethane Enclosure: ABS + PC
Display Type	5 LEDs
Operating Distance	50 m
Communication Network Type	Wireless: Zigbee
Transmission Frequency	2.4 GHz
Maximum Sensing Distance	100 m in free field
Response Time	< 500 ms at simplex
Charging Time	10800 s 0 s
Autonomy	150 h Li-Ion (Lithium-Ion) 100 h
Mechanical Durability	1000000 cycles
Width	85 mm
Height	193 mm
Depth	43 mm
Net Weight	0.3 kg

Environment

Radio Agreement	IC FCC
Ip Degree Of Protection	IP65
Ambient Air Temperature For Operation	-20...55 °C
Ambient Air Temperature For Storage	-20...45 °C
Operating Altitude	0...2000 m
Storage Altitude	0...3000 m

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Relative Humidity	0...95 % at -20...60 °C operating
Product Certifications	CE

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.3 cm
Package 1 Width	10.5 cm
Package 1 Length	21.5 cm
Package 1 Weight	423.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	18
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	8.087 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Dimensions Drawings

Dimensions

