

Product datasheet

Specifications



limit switch head ZCKE - steel roller plunger reinforced

Local distributor code: 2205298 ZCKE67

Main

Range of product	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCKE
Head type	Plunger head
Product compatibility	XCKJ
Associated body	ZCKJ1 ZCKJ2 ZCKJ41H7 ZCKJ9H29 ZCKJ8H29 ZCKJ6H29 ZCKJ5H7 ZCKJD39H7 ZCKJ21H29 ZCKJ21H7 ZCKJ6 ZCKJ7 ZCKJD35H7 ZCKJD35 ZCKJD37 ZCKJ21 ZCKJ5 ZCKJ41 ZCKJ7H7 ZCKJ4H29 ZCKJ7H29 ZCKJ41H29 ZCKJD37H7 ZCKJ11 ZCKJ2H29 ZCKJ8 ZCKJ11H7 ZCKJ2H7 ZCKJ4 ZCKJD31 ZCKJ6H7 ZCKJ1H29 ZCKJ9 ZCKJD35H29 ZCKJ9H7 ZCKJ8H7 ZCKJ5H29 ZCKJ4H7 ZCKJD39 ZCKJD39H29 ZCKJ11H29 ZCKJD31H7 ZCKJD37H29 ZCKJ1H7 ZCKJD31H29
Movement of operating head	Linear

Type of operator	Roller plunger spring return metal (reinforced)
Type of approach	Lateral approach, 2 directions

Complementary

Switch actuation	By 30° cam
Positive opening	With
Head material	Metal

Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Standard environment

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	161 g
Package 1 Height	4.2 cm
Package 1 width	4.5 cm
Package 1 Length	8.7 cm
Unit Type of Package 2	PAL
Number of Units in Package 2	768
Package 2 Weight	139.348 kg
Package 2 Height	77 cm
Package 2 width	60 cm
Package 2 Length	80 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------