

# Product datasheet

Specifications



limit switch lever ZCKY - th.plastic  
roller lever variable length -  
-40..70°C

Local distributor code: 2205450 ZCKY41

## Main

Range of product	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or component type	Limit switch lever
Device short name	ZCKY
Product compatibility	XCKS XCKL XCKM XCKJ
Associated head	ZCKE05 ZCKD05
Movement of operating head	Rotary
Type of operator	Roller lever spring return thermoplastic (variable length)
Type of approach	Lateral approach

## Complementary

Switch actuation	By 30° cam
Positive opening	Without

## Environment

Ambient air temperature for operation	-25...70 °C for standard environment -40...70 °C for low temperature
Ambient air temperature for storage	-40...70 °C standard environment -40...70 °C low temperature
Environmental characteristic	Low temperature Standard environment

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	24 g
Package 1 Height	1.5 cm
Package 1 width	2 cm
Package 1 Length	10 cm

<b>Unit Type of Package 2</b>	S01
<b>Number of Units in Package 2</b>	100
<b>Package 2 Weight</b>	2.625 kg
<b>Package 2 Height</b>	15 cm
<b>Package 2 width</b>	15 cm
<b>Package 2 Length</b>	40 cm
<b>Unit Type of Package 3</b>	P06
<b>Number of Units in Package 3</b>	1600
<b>Package 3 Weight</b>	50.5 kg
<b>Package 3 Height</b>	77 cm
<b>Package 3 width</b>	80 cm
<b>Package 3 Length</b>	60 cm

## Offer Sustainability

<b>Sustainable offer status</b>	Green Premium product
<b>REACH Regulation</b>	<a href="#">REACH Declaration</a>
<b>EU RoHS Directive</b>	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
<b>Mercury free</b>	Yes
<b>RoHS exemption information</b>	<a href="#">Yes</a>
<b>Environmental Disclosure</b>	<a href="#">Product Environmental Profile</a>

## Contractual warranty

<b>Warranty</b>	18 months
-----------------	-----------