

Product data sheet

Specifications



discrete input module Modicon Quantum - 16 inputs - 24 V AC

140DAI34000C

⚠ Discontinued on: May 11, 2021

⚠ To be end-of-service on: Dec 31, 2029

⚠ Discontinued

Main

Range Of Product	Modicon Quantum automation platform
Product Or Component Type	VAC discrete input modules
Software Name	Unity Pro Concept ProWORX 32
Discrete Input Number	16

Complementary

Group Of Channels	16
Addressing Requirement	1 input word
Discrete Input Voltage	24 V AC
Input Current	12 mA 57...63 Hz 10.7 mA 47...53 Hz
Voltage State 1 Guaranteed	16...30 V AC 57...63 Hz 18...30 V AC 47...53 Hz
Voltage State 0 Guaranteed	0...6 V 57...63 Hz 0...5 V 47...53 Hz
Input Impedance	2600 Ohm capacitive 57...63 Hz 3100 Ohm capacitive 47...53 Hz
Network Frequency Limits	47...63 Hz
Maximum Leakage Current	1.9 mA
Absolute Maximum Input	30 V continuous 32 V 10 s 50 V 1 cycle
Response Time	4.9...0.75 ms x line cycle Off-On 7.3...12.3 ms On-Off
Isolation Between Channels	1780 Vrms for 1 minute
Isolation Between Channels And Bus	1780 Vrms for 1 minute
Bus Current Requirement	180 mA
Maximum Power Dissipation In W	5.5 W
Local Signalling	for bus communication is present (Active) 1 LED (green) for external fault detected (F) 1 LED (red) for input status 16 LEDs (green)
Marking	CE
Module Format	Standard

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Net Weight	0.66 lb(US) (0.3 kg)
------------	----------------------

Environment

Protective Treatment	Conformal coating Humiseal 1A33
Standards	UL 508 CSA C22.2 No 142
Product Certifications	FM Class 1 Division 2 cUL
Resistance To Electrostatic Discharge	4 kV contact IEC 801-2 8 kV on air IEC 801-2
Resistance To Electromagnetic Fields	9.14 V/m (10 V/m) 80...2000 MHz IEC 801-3
Ambient Air Temperature For Operation	32...140 °F (0...60 °C)
Ambient Air Temperature For Storage	-40...185 °F (-40...85 °C)
Relative Humidity	95 % without condensation
Operating Altitude	<= 16404.2 ft (5000 m)

Ordering and shipping details

Category	18155-QUANTUM I/O & POWER SUPPLIES
Discount Schedule	PC21
Gtin	3595861135901
Returnability	No
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.97 in (5 cm)
Package 1 Width	6.30 in (16 cm)
Package 1 Length	12.20 in (31 cm)
Package 1 Weight	15.24 oz (432 g)
Unit Type Of Package 2	S02
Number Of Units In Package 2	2
Package 2 Height	5.91 in (15 cm)
Package 2 Width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)
Package 2 Weight	2.76 lb(US) (1.25 kg)
Unit Type Of Package 3	S03
Number Of Units In Package 3	2
Package 3 Height	11.81 in (30 cm)
Package 3 Width	11.81 in (30 cm)
Package 3 Length	15.75 in (40 cm)
Package 3 Weight	30.48 oz (864 g)


Contractual warranty

Warranty	18 months
----------	-----------

Dimensions Drawings

Racks for Modules Mounting

Dimensions of Modules and Racks




- (1) 2 slots
- (2) 3 slots
- (3) 4 slots
- (4) 6 slots
- (5) 10 slots
- (6) 16 slots

Connections and Schema

24 Vac Discrete Input Module

Wiring Diagram



N/C Not Connected