

Product data sheet

Specifications



Unity M1E processor - RS232/485 - Ethernet - USB - I/O bus

171CBU98090

Product availability: Stock - Normally stocked in distribution facility

Main

Range Of Product	Modicon Momentum automation platform
Product Or Component Type	Processor
Product Compatibility	Modicon STB I/O
Integrated Connection Type	Ethernet USB port

Complementary

Concept	Transparent Ready class B
Web Services	CPU status Ethernet statistics Bandwidth monitoring Home pages Properties
Software Designation	Unity Pro
Communication Service	Modbus messaging 125 words, 200 I/O message per second Global Data, 1600 I/O message per second Modbus TCP I/O Scanner and Messaging
Processor Name	Spear 320s
Word Length	32 bit
Supply Voltage Limits	4.75...5.25 V
Clock Frequency	333 MHz
Topology	Multidrop Modbus Star Modbus TCP
Communication Port Protocol	Modbus RS485/RS232 - 1 RJ45 19200 bps - 2-wire Modbus TCP ETHERNET - 1 RJ45 10/100 Mbps - twisted shielded pairs cable CAT 5E UTP
Method Of Access	Client/server Master/slave
Control Parameter	CRC-16 for Modbus CRC-32 for Modbus TCP/IP
Addressing	1...247 Modbus Unique IEEE global address Modbus TCP
Fail State	Safe I/O mode
Memory Description	Program memory IEC 3584 kB Program memory LL984 3584 kB
Register Words	26048
I/O Limit Processor Capacity	2048 inputs/2048 outputs
Number Of Devices	32 Modbus

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Exact Time For 1 Kinstruction	83 ns
Local Signalling	for processor running (RUN) 1 LED (green) for processor or system fault (ERR) 1 LED (red) for I/O module fault (I/O) 1 LED (red) for channel 0 operating (CH0) 1 LED (yellow) for data rate (ETH 100) 1 LED (green) for data rate (ETH LINK) 1 LED (green) for status of Ethernet network (ETH STS) 1 LED (green)
Marking	CE
Current Consumption	500 mA 5 V DC
Module Format	Standard
Product Mounting	35 mm symmetrical DIN rail
Height	2.39 in (60.6 mm)
Width	5.67 in (144 mm)
Depth	2.11 in (53.47 mm)
Net Weight	0.36 lb(US) (0.163 kg)

Environment

Material	Lexan
Dielectric Strength	0 V not isolated RS485/RS232 5000 V for 1 minute ETHERNET
Product Certifications	FM C-tick
Standards	UL 508 CSA C22.2 No 142 EN/IEC 61131-2
Ip Degree Of Protection	IP20
Shock Resistance	15 gn 11 ms sinusoidal vibrations
Resistance To Electrostatic Discharge	6 kV contact EN/IEC 61131-2 zone B 6 kV contact IACS E10 8 kV on air EN/IEC 61000-4-2
Resistance To Electromagnetic Fields	13.72 V/m (15 V/m) 80...2700 MHz EN/IEC 61000-4-3
Ambient Air Temperature For Operation	32...140 °F (0...60 °C)
Ambient Air Temperature For Storage	-40...185 °F (-40...85 °C)
Relative Humidity	5...96 %
Operating Altitude	<= 6561.68 ft (2000 m)

Ordering and shipping details

Category	US1PC3118206
Discount Schedule	PC31
Gtin	3595864171395
Returnability	Yes
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Package 1 Height	2.95 in (7.500 cm)
Package 1 Width	4.41 in (11.200 cm)
Package 1 Length	8.15 in (20.700 cm)
Package 1 Weight	8.36 oz (237.000 g)
Unit Type Of Package 2	S03
Number Of Units In Package 2	8
Package 2 Height	11.81 in (30.000 cm)
Package 2 Width	11.81 in (30.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	5.26 lb(US) (2.385 kg)

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

China Rohs Regulation

[China RoHS declaration](#)

Weee


The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

California Proposition 65

WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Dimensions Drawings

Processor and Option Adapter on a Typical Base



Mounting and Clearance

Mounting on a Wall

