





# Transformer, dry type, encapsulated, 1kVA, 1 phase, multiple voltages, 7A, 115C rise

1S67F

Product availability: Stock - Normally stocked in distribution

Price\*: 1,593.00 USD

#### Main

Product Or Component Type	Dry Sealed Transformer
Primary To Secondary Voltage	190/200/208/220 x 380/400/416/440 V 110/220 V
Full Capacity Taps	0

### Complementary

Enclosure Code	7A
Phase	1 phase
Power Rating	1 kVA
Temperature Rise	115 °C
Height	8.13 in (206.50 mm)
Width	6.94 in (176.28 mm)
Depth	5.31 in (134.87 mm)
Enclosure Mounting	Wall mounted
Enclosure Material	Painted sheet steel

#### **Environment**

Enclosure Type	NEMA 3R
Insulation Temperature	356 °F (180 °C)
Product Certifications	TÜV CSA cULus UL Listed

### Ordering and shipping details

Category	US10PE216277
Discount Schedule	0PE2
Gtin	785901068730
Returnability	Yes
Country Of Origin	US

## **Packing Units**

Unit Type Of Package 1	PCE	
------------------------	-----	--

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Number Of Units In Package 1	1
Package 1 Height	8.90 in (22.606 cm)
Package 1 Width	10.20 in (25.908 cm)
Package 1 Length	11.20 in (28.448 cm)
Package 1 Weight	21.20 lb(US) (9.616 kg)
Unit Type Of Package 2	PAL
Number Of Units In Package 2	48
Package 2 Height	40.00 in (101.6 cm)
Package 2 Width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)
Package 2 Weight	1200.00 lb(US) (544.31 kg)

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>⊘</b>	Reach Free Of Svhc
<b>⊘</b>	Toxic Heavy Metal Free
<b>⊘</b>	Mercury Free
<b>⊘</b>	Rohs Exemption Information Yes
<b>⊘</b>	Pvc Free

#### **Certifications & Standards**

REACh Declaration
Compliant
EU RoHS Declaration
China RoHS declaration
Pro-active China RoHS declaration (out of China RoHS legal scope)
Product Environmental Profile
No need of specific recycling operations
WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov