

# Product data sheet

Specifications



Transformer, dry type,  
encapsulated, 1kVA, 1 phase,  
208V primary, 120/240V  
secondary, 7A, 115C rise

1S7F

Product availability: Stock - Normally stocked in distribution facility

Price\*: 1,472.00 USD

## Main

Product Or Component Type	Dry Sealed Transformer
Primary To Secondary Voltage	208 V 120/240 V
Full Capacity Taps	0

## Complementary

Enclosure Code	7A
Phase	1 phase
Power Rating	1 kVA
Temperature Rise	115 °C
Height	8.13 in (206.50 mm)
Width	6.94 in (176.28 mm)
Depth	5.31 in (134.87 mm)
Enclosure Mounting	Wall mounted
Enclosure Material	Painted sheet steel

## Environment

Enclosure Type	NEMA 3R
Insulation Temperature	356 °F (180 °C)
Product Certifications	UL Listed CSA cULus

## Ordering and shipping details

Category	US10PE216277
Discount Schedule	0PE2
Gtin	785901099451
Returnability	Yes
Country Of Origin	US

## Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 1	1
Package 1 Height	9.00 in (22.86 cm)
Package 1 Width	10.10 in (25.654 cm)
Package 1 Length	11.30 in (28.702 cm)
Package 1 Weight	21.20 lb(US) (9.616 kg)
Unit Type Of Package 2	PAL
Number Of Units In Package 2	48
Package 2 Height	40.00 in (101.6 cm)
Package 2 Width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)
Package 2 Weight	1171.05 lb(US) (531.18 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
✓	Pvc Free	

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="#">www.P65Warnings.ca.gov</a>