

Product data sheet

Specifications

SQUARE D



Single manual starter, Type F, 277VAC, 16A, 1 pole, sheet steel enclosure, toggle switch operator, green indicator

2510FF1PG

Discontinued

Discontinued on: Sep 15, 2023

To be end-of-service on: Dec 31, 2024

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

| | |
|---------------------|----------------------------|
| Product | Single Unit Manual Starter |
| Type | F |
| Overload Relay Type | Melting alloy |

Complementary

| | |
|-----------------------|---|
| Current Rating | 16 A |
| Cable Entry | Without |
| Horsepower Rating | 1 hp 115 V AC 1 hp 230 V AC 1 hp 277 V AC |
| Voltage Rating | 277 V AC |
| Number Of Poles | 1P |
| Control Unit | Toggle switch |
| Number Of Phases | 1 phase |
| Pilot Light | Green indicator |
| Reset | Manual |
| Motor Starter Type | Non reversing |
| Electrical Connection | Screw clamp terminals |
| Wire Gauge | AWG 14...AWG 12 copper |
| Height | 4.5 in (114.30 mm) |
| Width | 2.75 in (69.85 mm) |
| Depth | 2.19 in (55.63 mm) |

Environment

| | |
|------------------------|---|
| Product Certifications | UL listed file E42243 CCN NLRV CSA LR25490 class 3211 05 |
| Nema Enclosure Rating | Not rated (flush plate) sheet steel standard size |

Ordering and shipping details

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|-------------------|--------------|
| Category | US10CP121101 |
| Discount Schedule | 0CP1 |
| Gtin | 785901833406 |
| Returnability | No |
| Country Of Origin | MX |

Packing Units

| | |
|------------------------------|---------------------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 5.00 in (12.7 cm) |
| Package 1 Width | 2.50 in (6.35 cm) |
| Package 1 Length | 3.00 in (7.62 cm) |
| Package 1 Weight | 7.47 oz (211.828 g) |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Pvc Free

| | |
|---------------------------|---|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Not compliant |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information. |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |