

# Product data sheet

Specifications



## FHP Manual Starter - Flush Mount - 1P - Key Operated - Red Indicator - 277VAC

2510FF3P

⚠ Discontinued

### Main

Product	Single Unit Manual Starter
Type	F
Overload Relay Type	Melting alloy

### Complementary

Current Rating	16 A
Cable Entry	Without
Horsepower Rating	1 hp 115 V AC 1 hp 230 V AC 1 hp 277 V AC
Voltage Rating	277 V AC
Number Of Poles	1P
Control Unit	Key
Number Of Phases	1 phase
Pilot Light	Red indicator
Reset	Manual
Motor Starter Type	Non reversing
Electrical Connection	Screw clamp terminals
Wire Gauge	AWG 14...AWG 12 copper
Height	4.5 in (114.30 mm)
Width	2.75 in (69.85 mm)
Depth	2.19 in (55.63 mm)

### Environment

Product Certifications	UL listed file E42243 CCN NLRV CSA LR25490 class 3211 05
Nema Enclosure Rating	Not rated (flush plate) sheet steel standard size

### Ordering and shipping details

Category	21101-2510,2511,2512 F
Discount Schedule	CP1
Gtin	00785901553854

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Returnability	No
Country Of Origin	MX

### Contractual warranty

Warranty	18 months
----------	-----------