

# Product data sheet

Specifications



## FHP Manual Starter - NEMA 1 Oversized - 1P-Toggle Operated-No Indicator-277VAC

2510FGJ1

Discontinued on: Jun 30, 2020

Discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

### Main

Product	Single Unit Manual Starter
Type	F
Overload Relay Type	Melting alloy

### Complementary

Current Rating	16 A
Cable Entry	0.5" or 0.75" knock-outs (2 side)
Horsepower Rating	1 hp 115 V AC 1 hp 230 V AC 1 hp 277 V AC
Voltage Rating	277 V AC
Number Of Poles	1P
Control Unit	Toggle switch
Number Of Phases	1 phase
Pilot Light	No indicator
Reset	Manual
Motor Starter Type	Non reversing
Electrical Connection	Screw clamp terminals
Wire Gauge	AWG 14...AWG 12 copper
Height	4.25 in (107.95 mm)
Width	2.88 in (73.15 mm)
Depth	2.75 in (69.85 mm)

### Environment

Product Certifications	UL listed file E42243 CCN NLRV CSA LR25490 class 3211 05
Nema Enclosure Rating	NEMA 1 Plastic oversized

### Ordering and shipping details

Category	US10CP121101
Discount Schedule	OCP1
Gtin	00785901486527

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Returnability	No
Country Of Origin	MX

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

### Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

 Reach Free Of Svhc

 Pvc Free

Eu Rohs Directive

Not compliant

China Rohs Regulation

[China RoHS declaration](#)  
Product out of China RoHS scope. Substance declaration for your information.

California Proposition 65

WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)