

Product data sheet

Specifications

SQUARE D



Obsolete - FHP Manual Starter Special - Open - 1P - Toggle Operated - 277VAC

2510FO1S1

! Discontinued

Main

Product	Single Unit Manual Starter
Type	F
Overload Relay Type	Melting alloy

Complementary

Current Rating	16 A
Cable Entry	Without
Horsepower Rating	1 hp 115 V AC 1 hp 230 V AC 1 hp 277 V AC
Voltage Rating	277 V AC
Number Of Poles	1P
Control Unit	Toggle switch
Number Of Phases	1 phase
Pilot Light	No indicator
Reset	Manual
Motor Starter Type	Non reversing
Electrical Connection	Screw clamp terminals
Wire Gauge	AWG 14...AWG 12 copper
Height	4.13 in (104.90 mm)
Width	1.69 in (42.93 mm)
Depth	2.22 in (56.39 mm)

Environment

Product Certifications	UL recognized E42243 CCN NLRV2 CSA LR25490 class 3211 05
Nema Enclosure Rating	Not rated (open device)

Ordering and shipping details

Category	21101-2510,2511,2512 F
Discount Schedule	CP1
Returnability	No

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Country Of Origin	MX
-------------------	----

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	6.40 oz (181.437 g)

Contractual warranty

Warranty	18 months
----------	-----------