

# Product data sheet

Specifications

SQUARE D



## Special Manual Switch - Open - 2P - Toggle Operated - No Indicator - 600VAC

2510KO1Y7

! Discontinued

### Main

Product	Single Unit Manual Switch
Type	K

### Complementary

Current Rating	30 A
Horsepower Rating	2 hp 115 V AC 2 hp 230 V AC 3 hp 460 V AC 3 hp 575 V AC 1 hp 90 V DC 2 hp 115 V DC 1.5 hp 230 V DC
Maximum Voltage Rating	600 V AC 230 V DC
Number Of Poles	2P
Control Unit Type	Toggle
Number Of Phases	1 phase
Pilot Light	No indicator
Starter Type	Non reversing
Electrical Connection	Screw clamp terminals
Wire Gauge	AWG 14...AWG 10 copper
Height	4.13 in (104.90 mm)
Width	1.69 in (42.93 mm)
Depth	2.34 in (59.44 mm)

### Environment

Certifications	UL recognized E42243 CCN NLRV2 CSA LR25490 class 3211 05
Nema Enclosure Rating	Not rated (open device)

### Ordering and shipping details

Category	21102-2510,2511,2512 K
Discount Schedule	CP1
Returnability	No
Country Of Origin	MX

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	8.00 oz (226.796 g)

## Contractual warranty

Warranty	18 months
----------	-----------