

Product data sheet

Specifications



Manual starter, integral horsepower, NEMA M1P, 600VAC, 2 pole, 5HP at 230VAC, 1 phase, no indicator, NEMA 4/4X

2510MCW2

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 1,144.34 USD

Main

| | |
|-----------|----------------|
| Product | Manual Starter |
| Type | M |
| Nema Size | M-1P |

Complementary

| | |
|----------------------------------|--|
| Control Unit | Push-button |
| Pilot Light | No indicator |
| Horsepower Rating | 3 hp 115 V AC, 1 phase 5 hp 230 V AC, 1 phase |
| Voltage Rating | 600 V AC |
| Number Of Poles | 2P |
| Starter Type | Non reversing |
| Electrical Connection | Box lugs |
| Overload Relay Type | Melting alloy |
| Number Of Thermal Units Required | 1 |
| Wire Gauge | AWG 14...AWG 6 copper |
| Auxiliary Contacts | Without |
| Height | 12.13 in (308.10 mm) |
| Width | 6.5 in (165.10 mm) |
| Depth | 6.41 in (162.81 mm) |

Environment

| | |
|-----------------------|---|
| Certifications | CSA LR60905 class 3211 05 UL listed file E42243 CCN NLRV |
| Nema Enclosure Rating | NEMA 4/4X glass polyester |

Ordering and shipping details

| | |
|-------------------|--------------|
| Category | US10CP121103 |
| Discount Schedule | 0CP1 |
| Gtin | 785901182740 |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|-------------------|-----|
| Returnability | Yes |
| Country Of Origin | MX |

Packing Units

| | |
|------------------------------|------------------------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 6.90 in (17.526 cm) |
| Package 1 Width | 8.20 in (20.828 cm) |
| Package 1 Length | 13.20 in (33.528 cm) |
| Package 1 Weight | 8.04 lb(US) (3.647 kg) |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability




Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

| | |
|--|---|
|  Mercury Free | |
|  Rohs Exemption Information | Yes |
|  Pvc Free | |
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Compliant with Exemptions |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information. |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |