

Product data sheet

Specifications



Transformer, dry type,
encapsulated, 25kVA, 1 phase,
240x480V primary, 120/240V
secondary, 15B, 115C rise

25S1F

Product availability: Stock - Normally stocked in distribution facility

Price*: 7,639.00 USD

Main

Product Or Component Type	Dry Sealed Transformer
Primary To Secondary Voltage	240 x 480 V 120/240 V
Full Capacity Taps	0

Complementary

Enclosure Code	15B
Phase	1 phase
Power Rating	25 kVA
Temperature Rise	115 °C
Height	20 in (508.00 mm)
Width	15 in (381.00 mm)
Depth	13.5 in (342.90 mm)
Enclosure Mounting	Wall mounted
Enclosure Material	Painted sheet steel

Environment

Enclosure Type	NEMA 3R
Insulation Temperature	356 °F (180 °C)
Product Certifications	cULus UL Listed CSA

Ordering and shipping details

Category	US10PE216277
Discount Schedule	0PE2
Gtin	785901225430
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 1	1
Package 1 Height	16.00 in (40.64 cm)
Package 1 Width	19.30 in (49.022 cm)
Package 1 Length	15.30 in (38.862 cm)
Package 1 Weight	385.00 lb(US) (174.633 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
✓	Pvc Free	

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov