

# Product data sheet

Specifications



## voltage release Compact MN - 110..130 V AC 50/60Hz

29406

! Discontinued

### Main

Range	ComPact
Range Of Product	NSJ400...600 NS400...630 DC NB400...600 NS400...630 NSF150...250 NS100...250 NS125E NR400...630 NR100...250 NS100...250 DC
Device Short Name	MN
Product Or Component Type	Voltage release
Device Application	Control
Voltage Release Type	Undervoltage release
[Uc] Control Circuit Voltage	110...130 V AC 50/60 Hz
Range Compatibility	ComPact ComPact NS ComPact Compact NB ComPact Compact NR ComPact Compact NSF ComPact Compact NSJ

### Complementary

Operating Threshold	0.35...0.7 Un opening 0.85 Un closing
Response Time	< 50 ms
Supply Holding Power	< 5 VA
Auxiliary Connection Terminal	screw terminal 0.00...0.00 in² (0...1.5 mm²)

### Ordering and shipping details

Category	01103-H,J,COMPACT NS UL/IEC CIRCUIT BREAKER ACCESSORIES
Discount Schedule	DE2
Gtin	00785901367338
Returnability	No
Country Of Origin	FR

### Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 1	1
------------------------------	---

## Contractual warranty

Warranty	18 months
----------	-----------