

# Product data sheet

Specifications



NEMA Motor Starter, Type S,  
replacement coil, 347 VAC 60 Hz,  
NEMA Size 00, 0 and 1 starters  
and 8903SM lighting

3104140055

! Discontinued

! Discontinued on: Nov 11, 2020

! End-of-service on: Dec 31, 2020

## Main

Product Or Component Type	Coil
Accessory / Separate Part Destination	Class 8502 type SA (series A)/SB/SC contactor Class 8536 type SA (series A)/SB/SC starter Class 8903 type SM lighting contactor

## Complementary

[Ue] Rated Operational Voltage	347 V AC 60 Hz
Inrush Power In Va	245 VA
Average Consumption	27 VA
Height	2.15 in (54.7 mm)
Width	3.21 in (81.5 mm)
Depth	1.90 in (48.3 mm)

## Ordering and shipping details

Category	18079-SPARE PARTS DISCOUNT CP10
Discount Schedule	CP10
Gtin	00785901292104
Returnability	No
Country Of Origin	MX

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

**Eu Rohs Directive**

Not applicable, out of EU RoHS legal scope

---