

# Product data sheet

Specifications

SQUARE D



NEMA Motor Starter, Type S, replacement coil, 24 VAC 60 Hz, 2 or 3 pole, NEMA size 2 starter and 8903SP lighting

3106340916

Discontinued

Discontinued on: Dec 18, 2023

Product availability: Stock - Normally stocked in distribution facility

## Main

Product Or Component Type	Coil
Accessory / Separate Part Destination	Class 8502 type SD contactor Class 8903 type SP lighting contactor

## Complementary

Nema Size	2
[Ue] Rated Operational Voltage	24 V AC 60 Hz
Inrush Power In Va	311 VA
Average Consumption	37 VA
Height	2.61 in (66.2 mm)
Width	3.98 in (101.1 mm)
Depth	2.43 in (61.7 mm)

## Ordering and shipping details

Category	US10CP118061
Discount Schedule	0CP1
Gtin	785901229766
Returnability	Yes
Country Of Origin	MX

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.70 in (6.858 cm)
Package 1 Width	2.60 in (6.604 cm)
Package 1 Length	4.10 in (10.414 cm)
Package 1 Weight	12.96 oz (367.41 g)

## Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

**Eu Rohs Directive**

Not applicable, out of EU RoHS legal scope

---