

Product data sheet

Specifications



NEMA Motor Starter, Type S, replacement coil, 208VAC 60Hz, 2 or 3 pole, NEMA size 3 starter and 8903SQ lighting

3107440044

Product availability: Stock - Normally stocked in distribution facility

Price*: 254.00 USD

Main

Product Or Component Type	Coil
Accessory / Separate Part Destination	Class 8502 type SE contactor Class 8903 type SQ lighting contactor Class 8910 type DPA12/SYD138 contactor

Complementary

Nema Size	3
[Ue] Rated Operational Voltage	208 V AC 60 Hz
Inrush Power In Va	700 VA
Average Consumption	46 VA
Height	2.87 in (73 mm)
Width	2.56 in (65 mm)
Depth	0.08 in (2.093 mm)

Ordering and shipping details

Category	US1CP1018079
Discount Schedule	CP10
Gtin	785901226055
Returnability	Yes
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.10 in (5.334 cm)
Package 1 Width	2.80 in (7.112 cm)
Package 1 Length	3.40 in (8.636 cm)
Package 1 Weight	12.80 oz (362.874 g)

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive	Not applicable, out of EU RoHS legal scope
-------------------	--
