

Product data sheet

Specifications

SQUARE D



NEMA Motor Starter, Type S,
replacement coil, 220/240VAC
50/60Hz, 2 or 3 pole, NEMA size 3
starter and 8903SQ lighting

3107440047

Product availability: Stock - Normally stocked in distribution facility

Price*: 254.00 USD

Main

Product Or Component Type	Coil
Accessory / Separate Part Destination	Class 8502 type SE contactor Class 8903 type SQ lighting contactor Class 8910 type DPA12/SYD138 contactor

Complementary

Nema Size	3
[Ue] Rated Operational Voltage	240 V AC 60 Hz 220 V AC 50 Hz
Inrush Power In Va	700 VA 678 VA
Average Consumption	47 VA 46 VA
Height	2.87 in (73 mm)
Width	2.56 in (65 mm)
Depth	0.08 in (2.093 mm)

Ordering and shipping details

Category	US1CP1018079
Discount Schedule	CP10
Gtin	785901110880
Returnability	Yes
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.10 in (5.334 cm)
Package 1 Width	2.80 in (7.112 cm)
Package 1 Length	3.30 in (8.382 cm)
Package 1 Weight	13.28 oz (376.482 g)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Contractual warranty

Warranty

18 months

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Not applicable, out of EU RoHS legal scope
