

# Product data sheet

Specifications

SQUARE D



NEMA Motor Starter, Type S, replacement coil, 277VAC 60Hz, 2 or 3 pole, NEMA size 3 starter and 8903SQ lighting

3107440049

Discontinued

Discontinued on: Jun 30, 2023

Product availability: Stock - Normally stocked in distribution facility

## Main

Product Or Component Type	Coil
Accessory / Separate Part Destination	Class 8502 type SE contactor Class 8903 type SQ lighting contactor Class 8910 type DPA12/SYD138 contactor

## Complementary

Nema Size	3
[Ue] Rated Operational Voltage	277 V AC 60 Hz
Inrush Power In Va	700 VA
Average Consumption	46 VA
Height	2.87 in (73 mm)
Width	2.56 in (65 mm)
Depth	0.08 in (2.093 mm)

## Ordering and shipping details

Category	US1CP1018079
Discount Schedule	CP10
Gtin	785901110538
Returnability	Yes
Country Of Origin	MX

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.10 in (5.334 cm)
Package 1 Width	2.80 in (7.112 cm)
Package 1 Length	3.40 in (8.636 cm)
Package 1 Weight	13.12 oz (371.946 g)

## Contractual warranty

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Warranty

18 months

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Eu Rohs Directive	Not applicable, out of EU RoHS legal scope
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.