

# Product data sheet

Specifications



NEMA Motor Starter, Type S,  
replacement coil, 550/600 VAC  
50/60 Hz, 2 or 3 pole, NEMA size  
3 starter and 8903SQ lighting

3107440060

! Discontinued

! Discontinued on: Oct 11, 2021

Product availability: Stock - Normally stocked in distribution facility

## Main

Product Or Component Type	Coil
Accessory / Separate Part Destination	Class 8502 type SE contactor Class 8903 type SQ lighting contactor Class 8910 type DPA12/SYD138 contactor

## Complementary

Nema Size	3
[Ue] Rated Operational Voltage	600 V AC 60 Hz 550 V AC 50 Hz
Inrush Power In Va	678 VA 700 VA
Average Consumption	47 VA 46 VA
Height	2.87 in (73 mm)
Width	2.56 in (65 mm)
Depth	0.08 in (2.093 mm)

## Ordering and shipping details

Category	18079-SPARE PARTS DISCOUNT CP10
Discount Schedule	CP10
Gtin	00785901110491
Returnability	No
Country Of Origin	MX

## Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive	Not applicable, out of EU RoHS legal scope
-------------------	--

---