

Product data sheet

Specifications



NEMA Motor Starter, Type S,
replacement coil, 277 VAC 60 Hz,
NEMA Size 4 starters and 8903SV
lighting contactors

3109140049

! Discontinued

! Discontinued on: Nov 20, 2023

Product availability: Non-Stock - Not normally stocked in
distribution facility

Main

Product Or Component Type	Coil
Accessory / Separate Part Destination	Class 8502 type SF contactor Class 8903 type SV lighting contactor Class 8910 type SYD230 contactor

Complementary

Nema Size	4
[Ue] Rated Operational Voltage	277 V AC 60 Hz
Inrush Power In Va	1185 VA
Average Consumption	85 VA
Height	2.87 in (73 mm)
Width	2.56 in (65 mm)
Depth	2.47 in (62.7 mm)

Ordering and shipping details

Category	US1CP1018079
Discount Schedule	CP10
Gtin	785901493426
Returnability	No
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.56 in (6.5 cm)
Package 1 Width	2.48 in (6.3 cm)
Package 1 Length	2.87 in (7.3 cm)
Package 1 Weight	18.88 oz (535.239 g)

Contractual warranty

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Warranty

18 months

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Not applicable, out of EU RoHS legal scope
