Product data sheet

Specifications





Standard opening voltage release MX, ComPacT NS630b/NS3200, fixed, 24/30VDC, 24VAC, spare part

33659

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 755.00 USD

Main

Range	ComPacT
Range Of Product	ComPacT NS630b1600 new generation ComPacT NS1600b3200 new generation
Device Short Name	MX
Product Or Component Type	Voltage release
Device Application	Control
Voltage Release Type	Opening coil Instantaneous voltage release
Control Type	Standard
[Uc] Control Circuit Voltage	24 V AC 50 Hz 2430 V DC
Circuit Breaker Mounting Mode	Fixed
Range Compatibility	ComPact ComPact NS630b1600 ComPact ComPact NS1600b3200

Complementary

Operating Threshold	0.71.1 x Un opening
Response Time	50 ms +/- 10 % Compact NS630b1600
	50 ms +/- 10 % Compact NS1600b3200
	55 ms +/- 10 % MasterPact NT
	70 ms +/- 10 % MasterPact NW
Supply Holding Power	4.5 VA
Accessory / Separate Part	Spare part MasterPact NT
Category	Spare part MasterPact NW
	Spare part ComPacT NS630b1600 new generation
	Spare part ComPacT NS1600b3200 new generation

Ordering and shipping details

Category	US10DE201250	
Discount Schedule	0DE2	
Gtin	3303430336594	
Returnability	No	
Country Of Origin	US	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.30 in (3.3 cm)
Package 1 Width	2.36 in (6.0 cm)
Package 1 Length	3.31 in (8.4 cm)
Package 1 Weight	5.29 oz (150.0 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	3.54 in (9.0 cm)
Package 2 Width	7.28 in (18.5 cm)
Package 2 Length	5.20 in (13.2 cm)
Package 2 Weight	3.46 lb(US) (1.57 kg)
Unit Type Of Package 3	S03
Number Of Units In Package 3	120
Package 3 Height	11.81 in (30.0 cm)
Package 3 Width	11.81 in (30.0 cm)
Package 3 Length	15.75 in (40.0 cm)
Package 3 Weight	42.56 lb(US) (19.303 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov