
Product data sheet

Specifications



① Discontinued

Main

Product	Drive Isolation Transformer	
Enclosure Code	30D	
Enclosure Type	NEMA 2	
Insulation Temperature	428 °F (220 °C)	
Phase	3 phase	
Primary Voltage	575 V delta	
Power Rating	440 kVA	
Secondary Voltage	oltage 460Y/265 V	
Full Capacity Taps	Taps 2 5 % 1+ 1-	
Temperature Rise	150 °C	
Winding Material	Aluminium	

Ordering and shipping details

Category	16266-DRIVE ISOLATION TRANSFORMERS
Discount Schedule	PE2
Gtin	3606486127742
Returnability	No

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	1154.00 lb(US) (523.446 kg)

Contractual warranty

Warranty

18 months

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc

Toxic Heavy Metal Free	
Mercury Free	
Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov