# Product data sheet

Specifications





## ground fault protector GFP - 2 poles - 25A - 120..240V - 300mA SIE

60951

Discontinued on: Feb 17, 2021

① Discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Main

Range	Multi9	
Product Name	Multi9 GFP	
Product Or Component Type	Residual current circuit breaker (RCCB)	
Device Short Name	GFP	
Poles Description	2P	
Neutral Position	Left	
Line Rated Current	25 A	
Network Type	AC	
Earth-Leakage Sensitivity	300 mA	
Earth-Leakage Protection Time Delay	Instantaneous	
Earth-Leakage Protection Class	Type AC-SIE	
Rated Conditional Short-Circuit Current	10 kA	
Utilisation Category	AC-23A	

### Complementary

Network Frequency	50/60 Hz	
[Ue] Rated Operational Voltage	230/240 V AC 50 Hz 120/240 V AC 60 Hz	
[Uimp] Rated Impulse Withstand Voltage	6 kV	
Control Type	Toggle	
Local Signalling	Fault indication	
Connection Pitch	0.71 in (18 mm) between phases	
9 Mm Pitches	4	
Height	3.19 in (81 mm)	
Width	1.42 in (36 mm)	
Depth	2.95 in (75 mm)	
Net Weight	7.76 oz (220 g)	
Color	Gray	
Mechanical Durability	20000 cycles	
Provision For Padlocking	Padlockable	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Locking Options Description	Padlocking in OFF position
Connections - Terminals	Tunnel type terminals 0.000.05 in² (2.535 mm²) flexible Tunnel type terminals 0.000.05 in² (2.535 mm²) rigid
Tightening Torque	30.98 lbf.in (3.5 N.m)

### **Environment**

Standards	IEC 61008 UL 1053
Ip Degree Of Protection	IP20 conforming to IEC 60529 IP40 conforming to IEC 60529 IPxx B conforming to IEC 60529
Tropicalisation	2
Relative Humidity	95 % 131 °F (55 °C)
Ambient Air Temperature For Operation	-13140 °F (-2560 °C)
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)

# Ordering and shipping details

Category	US10DE200908	
Discount Schedule	0DE2	
Gtin	785901483175	
Returnability	No	
Country Of Origin	US	

## **Packing Units**

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	1.57 in (4 cm)	
Package 1 Width	3.35 in (8.5 cm)	
Package 1 Length	3.54 in (9 cm)	
Package 1 Weight	7.23 oz (205 g)	

### **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Product out of China RoHS scope. Substance declaration for your information.
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.