

Product data sheet

Specifications

SQUARE D

Green Premium™



Power Relay, SPST, 1NO and 0NC, 20 A resistive at 110 VDC, 6 VAC coil

8501CO21V35

Discontinued on: Dec 2, 2020

End-of-service on: Dec 31, 2020

Discontinued

Main

Product Range	Power Relay 8501C
Product Type	Power relay
Short Name	type C
[In] Rated Line Current	20 A
Device Application	Suited for controlling small single phase motors and other light loads
Switch Function	SPST
Contact Composition	1 NO
[Uc] Control Circuit Voltage	6 V AC 50/60 Hz
Maximum Switching Voltage	500 V DC

Complementary

Class Number	8501
Phase	1 phase
Terminal Connects	Screw clamp terminal
Wire Range	AWG 10 copper
Terminal Tightening Torque	11...15 lbf.in (1.24...1.69 N.m)
Coil Burden	10 VA
Mounting	Panel mounting

Environment

Ambient Temperature Range - Operational	-22...122 °F (-30...50 °C)
Product Certifications	UL listed file E78351 CCN NLDX CSA CE
Height	2.43 in (61.72 mm)
Width	2.5 in (63.50 mm)
Depth	2.18 in (55.37 mm)

Ordering and shipping details

Category	21131-8501 C
Discount Schedule	CP2

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Returnability	No
Country Of Origin	CN

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov