





Power Relay, Type C, DPDT, 2 normally open and 2 normally closed contacts, 20A resistive at 110 VDC, 120 VAC coil

8501CO22V20

Product availability: Stock - Normally stocked in distribution facility

Price\*: 102.48 USD

#### Main

Product Range	Power Relay 8501C	
Product Type	Power relay	
Short Name	type C	
[In] Rated Line Current	20 A	
Device Application	Suited for controlling small single phase motors and other light loads	
Switch Function	DPDT	
Contact Composition	2 NO/2 NC	
[Uc] Control Circuit Voltage	120 V AC 50/60 Hz	
Maximum Switching Voltage	um Switching Voltage 325 V DC	

## Complementary

Class Number	8501	
Phase	1 phase	
Terminal Connects	Screw clamp terminal	
Wire Range	AWG 10 copper	
Terminal Tightening Torque	1115 lbf.in (1.241.69 N.m)	
Coil Burden	10 VA	
Mounting	g Panel mounting	

### **Environment**

Ambient Temperature Range - Operational	-22122 °F (-3050 °C)	
Product Certifications	UL listed file E78351 CCN NLDX CSA CE	
Height	3.12 in (79.25 mm)	
Width	2.5 in (63.50 mm)	
Depth	2.53 in (64.26 mm)	

## Ordering and shipping details

Category US10CP221131

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Discount Schedule	0CP2	
Gtin	785901052241	
Returnability	Yes	
Country Of Origin	CN	

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.40 in (6.096 cm)
Package 1 Width	2.50 in (6.35 cm)
Package 1 Length	3.20 in (8.128 cm)
Package 1 Weight	11.20 oz (317.515 g)

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>Ø</b>	Reach Free Of Svhc	
<b>②</b>	Toxic Heavy Metal Free	
<b>Ø</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov