





Plug in relay, Type KF, flange mounted, 1 HP at 277 VAC, 10A resistive at 277 VAC, 3PDT, 3 NO, 3 NC, 24 VAC coil

8501KFR13V14

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 32.57 USD

Main

Product Range	8501K	
Product Type	Relay	
Relay Type	General purpose	
Mounting Type	Flange	
Contact Composition	3PDT	
[Uc] Control Circuit Voltage	24 V AC	
Manual Operator	Without test button	

Complementary

Horsepower Rating	1 hp 277 V AC
Maximum Switching Voltage	300 V AC 30 V DC
Contact Material	Silver alloy (AgNi)
Operating Time	20 ms - pick-up 20 ms - drop-out
Shape Of Pins	Spade

Environment

Ambient Temperature Range -	-40131 °F (-4055 °C)	
Operational		
Product Certifications	UL Recognized CSA	
	CE	
Height	2.75 in (69.85 mm)	
Width	1.4 in (35.56 mm)	
Depth	1.4 in (35.56 mm)	

Ordering and shipping details

Category	US10CP221145
Discount Schedule	0CP2
Gtin	785901304333
Returnability	No

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Country Of Origin US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.70 in (4.318 cm)
Package 1 Width	1.70 in (4.318 cm)
Package 1 Length	3.00 in (7.62 cm)
Package 1 Weight	3.04 oz (86.183 g)



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Reach Free Of Svhc



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov