Product data sheet

① Discontinued

Specifications



Plug-In Relay - 8 pin plug-in - 2 poles - 240VAC coil

8501KP12V24

() Discontinued on: Oct 20, 2020

Main

mann	
Product Range	8501K
Product Type	Relay
Relay Type	General purpose
Mounting Type	Socket
Contact Composition	DPDT
[Uc] Control Circuit Voltage	240 V AC
Pilot Light	No indicator
Manual Operator	Without test button

Complementary

Horsepower Rating	0.33 hp 120 V AC
	0.5 hp 240 V AC
Breaking Capacity	3 A 120 V AC inductive control circuit UL 508
	1.5 A 240 V AC inductive control circuit UL 508
	10 A 240 V AC resistive control circuit UL 508
	10 A 28 V DC resistive control circuit UL 508
	10 A 120 V AC resistive control circuit UL 508
Maximum Switching Voltage	300 V AC
	30 V DC
Contact Material	Silver tin oxide
Operating Time	12 ms - pick-up
	12 ms - drop-out
Shape Of Pins	Tubular
For Use With	8501NR51
	8501NR52

Environment

Ambient Temperature Range - Operational	-40131 °F (-4055 °C)
Product Certifications	CSA CE UL Listed UL Recognized
Height	2.66 in (67.56 mm)
Width	1.39 in (35.31 mm)
Depth	1.39 in (35.31 mm)

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Ordering and shipping details

Category	21141-8501 KP
Discount Schedule	CP2
Gtin	00785901480723
Returnability	No
Country Of Origin	CN

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov