# **Product data sheet**

Specifications







Plug in relay, Type R, miniature, 0.5 HP at 277 VAC, 8A resistive at 120 VAC, 14 blade, 4PDT, 4 NO, 4 NC, 12 VDC coil

8501RSD14V51

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Price\*: 35.01 USD

#### Main

Product Range	8501R
Product Type	Miniature Relay
Relay Type	Low voltage

## Complementary

Complementary	
Mounting Type	Socket
Contact Composition	4PDT
[Uc] Control Circuit Voltage	12 V DC
Pilot Light	No indicator
Manual Operator	Without test button
Horsepower Rating	0.33 120 V AC 0.5 277 V AC
Breaking Capacity	3 A 120 V AC inductive control circuit UL 508 1.5 A 240 V AC inductive control circuit UL 508 8 A 120 V AC resistive control circuit UL 508 6 A 277 V AC resistive control circuit UL 508 8 A 30 V DC resistive control circuit UL 508
Maximum Switching Voltage	300 V AC 30 V DC
Contact Material	Silver alloy, gold flashed
Operating Time	20 ms - pick-up 20 ms - drop-out
Shape Of Pins	Spade
For Use With	8501NR45
Height	1.10 in (27.9 mm)
Width	0.83 in (21 mm)
Depth	1.63 in (41.5 mm)

#### Environment

Ambient Temperature Range - Operational	-40131 °F (-4055 °C)
Product Certifications	UL Listed CSA CE UL Recognized

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

# Ordering and shipping details

Category	US10CP221143
Discount Schedule	0CP2
Gtin	785901559429
Returnability	No
Country Of Origin	US

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.90 in (4.826 cm)
Package 1 Width	1.90 in (4.826 cm)
Package 1 Length	3.10 in (7.874 cm)
Package 1 Weight	1.28 oz (36.287 g)
Unit Type Of Package 2	CAR
Number Of Units In Package 2	25
Package 2 Height	3.80 in (9.652 cm)
Package 2 Width	8.20 in (20.828 cm)
Package 2 Length	11.30 in (28.702 cm)
Package 2 Weight	2.82 lb(US) (1.279 kg)

## **Contractual warranty**

Warranty

18 months

# Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

### Well-being performance

Reach Free Of Svhc

Rohs Exemption Information Yes

## **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov