Product data sheet

Specifications





Relay, miniature plug in, 15 A, 2 pole, 110 VDC coil

8501RSD42V60

! Discontinued on: Jan 23, 2021

Product availability: Non-Stock - Not normally stocked in distribution facility

① Discontinued

Main

| Product Range | 8501R |
|---------------|-----------------|
| Product Type | Miniature Relay |
| Relay Type | Standard |

Complementary

| Mounting Type | Socket |
|------------------------------|---|
| Contact Composition | DPDT |
| [Uc] Control Circuit Voltage | 110 V DC |
| Pilot Light | No indicator |
| Manual Operator | Without test button |
| Horsepower Rating | 0.5 120 V AC 1 277 V AC |
| Breaking Capacity | 3 A 120 V AC inductive control circuit UL 508 1.5 A 240 V AC inductive control circuit UL 508 15 A 120 V AC resistive control circuit UL 508 10 A 277 V AC resistive control circuit UL 508 15 A 28 V DC resistive control circuit UL 508 |
| Maximum Switching Voltage | 300 V AC 30 V DC |
| Contact Material | Silver alloy, gold flashed |
| Operating Time | 20 ms - pick-up 20 ms - drop-out |
| Shape Of Pins | Spade |
| For Use With | 8501NR42 |
| Height | 1.07 in (27.3 mm) |
| Width | 0.83 in (21 mm) |
| Depth | 1.65 in (41.8 mm) |

Environment

| Ambient Temperature Range - Operational | -40131 °F (-4055 °C) |
|--|----------------------|
| Product Certifications | UL Listed |
| | UL Recognized |
| | CSA |
| | CE |

Ordering and shipping details

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| Category | US10CP221143 |
|-------------------|----------------|
| Discount Schedule | 0CP2 |
| Gtin | 00785901131373 |
| Returnability | No |
| Country Of Origin | CN |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|-----|
| Number Of Units In Package 1 | 1 |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Reach Free Of Svhc



Rohs Exemption Information

Yes

Certifications & Standards

| Reach Regulation | REACh Declaration |
|---------------------------------|--|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |