Product data sheet

Specifications







Relay, miniature plug in, 10 A, 4 pole, 24 VDC coil, pilot light, test

8501RSD44M1P14V53

() Discontinued on: Jan 27, 2022



Main

Product Range	8501R
Product Type	Miniature Relay
Relay Type	Standard

Complementary

Mounting Type	Socket
Contact Composition	4PDT
[Uc] Control Circuit Voltage	24 V DC
Pilot Light	Green indicator relay energised LED
Manual Operator	Test button
Horsepower Rating	0.5 120 V AC 1 277 V AC
Breaking Capacity	3 A 120 V AC inductive control circuit UL 508 1.5 A 240 V AC inductive control circuit UL 508 10 A 120 V AC resistive control circuit UL 508 6.67 A 277 V AC resistive control circuit UL 508 10 A 28 V DC resistive control circuit UL 508
Maximum Switching Voltage	300 V AC 30 V DC
Contact Material	Silver alloy, gold flashed
Operating Time	20 ms - pick-up 20 ms - drop-out
Shape Of Pins	Spade
For Use With	8501NR34
Height	1.07 in (27.3 mm)
Width	1.60 in (40.6 mm)
Depth	1.65 in (41.8 mm)

Environment

Ambient Temperature Range - Operational	-40131 °F (-4055 °C)
Product Certifications	UL Listed UL Recognized
	CSA CE

Ordering and shipping details

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Category	21143-8501 R
Discount Schedule	CP2
Gtin	785901676829
Returnability	No
Country Of Origin	CN

Packing Units

-	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.06 in (2.7 cm)
Package 1 Width	1.61 in (4.1 cm)
Package 1 Length	1.65 in (4.2 cm)
Package 1 Weight	2.56 oz (72.575 g)

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov