Product data sheet

Specifications







RELAY 600VAC 20AMP NEMA +OPTIONS

8501XMO60V08

() Discontinued on: Oct 11, 2019



Main

8501X
Master
Relay
20 A AC
6 NO 6 master contact cartridges
6P
208 V AC 60 Hz
600 V AC
Panel
-40160 °F (-4071 °C)
Screw clamp terminals
CSA CE UL Listed
15 ms - pick-up 16 ms - drop-out
3.5 in (88.90 mm)
2.23 in (56.64 mm)
5.16 in (131.06 mm)

Ordering and shipping details

Category	21158-8501 XO (AC)
Discount Schedule	CP2
Returnability	No
Country Of Origin	MX

Contractual warranty

Warranty

18 months

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov