

Product data sheet

Specifications



NEMA Motor Starter, Type S, nonreversing, Size 1, 27A, 3 HP at 230 VAC, 5 kA SCCR, 1 phase, 2 pole, melting alloy, 240 VAC coil, NEMA 1

8536SCG1V03

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 539.00 USD

Main

Product Type	Motor starter
Product Range	S
Starter Type	Non reversing

Complementary

Nema Size	1
Rated Current	27 A
Number Of Poles	2P
Maximum Voltage Rating	600 V AC
Phase	1 phase
Type Of Overload	Melting alloy 1
Horsepower Rating	3 HP 230 V AC 2 HP 115 V AC
Sccr	Circuit-breaker: 5 kA at 600 V AC Fuse: 5 kA at 600 V AC
Coil Voltage	220 V AC 50 Hz 240 V AC 60 Hz
Control Circuit Type	Common control circuit
Control Units	No control units
Pilot Light	Without pilot light
Auxiliary Contacts	Without
Terminal Type	Screw clamp terminals
Height	10.00 in (254.00 mm)
Width	6.00 in (152.40 mm)
Depth	5.56 in (141.22 mm)

Environment

Enclosure Type	NEMA 1 painted sheet steel
----------------	----------------------------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Certifications	UL Listed CSA NEMA
----------------	--------------------------

Ordering and shipping details

Category	US10CP121192
Discount Schedule	0CP1
Gtin	785901080169
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.60 in (16.764 cm)
Package 1 Width	6.40 in (16.256 cm)
Package 1 Length	10.60 in (26.924 cm)
Package 1 Weight	7.10 lb(US) (3.221 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability


Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Pvc Free

Reach Regulation	REACH Declaration
Eu Rohs Directive	Not compliant
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov