

Product data sheet

Specifications

SQUARE D



Non-Reversing Starter Size 1P, 2-Pole, Melting Alloy Overload, Nema 1 +Options

8536SCG2V84F4T

Discontinued

Main

Product Type	Starter
Product Range	S
Starter Type	Non reversing

Complementary

Nema Size	1P
Rated Current	27 A
Number Of Poles	2P
Maximum Voltage Rating	600 V AC
Phase	1 phase
Type Of Overload	Melting alloy 1
Horsepower Rating	3 HP 115 V AC 5 HP 230 V AC
Coil Voltage	120 V AC 60 Hz secondary circuit 208 V AC 60 Hz primary circuit
Control Circuit Type	Control circuit transformer
Control Units	No control units
Other Equipment	2 fuses (primary)
Terminal Type	Screw clamp terminals

Environment

Enclosure Type	NEMA 1 painted sheet steel
Certifications	NEMA CSA UL Listed

Ordering and shipping details

Category	21192-8502,36 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
Returnability	No
Country Of Origin	MX

Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	25.97 lb(US) (11.78 kg)

Contractual warranty

Warranty	18 months
----------	-----------