

# Product data sheet

Specifications

SQUARE D



## Non-Reversing Starter Size 1, 3-Pole, Motor Logic SSOLR, NEMA 1 +Options

8536SCG3V01CH30P1SX22

! Discontinued

### Main

|               |               |
|---------------|---------------|
| Product Type  | Starter       |
| Product Range | S             |
| Starter Type  | Non reversing |

### Complementary

|                        |                                                                        |
|------------------------|------------------------------------------------------------------------|
| Nema Size              | 1                                                                      |
| Rated Current          | 27 A                                                                   |
| Number Of Poles        | 3P                                                                     |
| Maximum Voltage Rating | 600 V AC                                                               |
| Phase                  | 3 phase                                                                |
| Type Of Overload       | Solid state Motor Logic class 10/20                                    |
| Horsepower Rating      | 7.5 HP 200 V AC<br>7.5 HP 230 V AC<br>10 HP 460 V AC<br>10 HP 575 V AC |
| Coil Voltage           | 24 V AC 60 Hz                                                          |
| Control Circuit Type   | Separate control circuit                                               |
| Control Units          | Selector switch (HAND-OFF-AUTO)                                        |
| Pilot Light            | Red indicator on incandescent                                          |
| Auxiliary Contacts     | 2 NO + 2 NC                                                            |
| Terminal Type          | Screw clamp terminals                                                  |

### Environment

|                |                            |
|----------------|----------------------------|
| Enclosure Type | NEMA 1 painted sheet steel |
| Certifications | CSA<br>NEMA<br>UL Listed   |

### Ordering and shipping details

|                   |                                  |
|-------------------|----------------------------------|
| Category          | 21192-8502,36 SC,SD(NOT S*R,T,W) |
| Discount Schedule | CP1                              |
| Returnability     | No                               |
| Country Of Origin | MX                               |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|