

Product data sheet

Specifications

SQUARE D



Non-Reversing Starter Size 1, 3-Pole, Melting Alloy Overload, Nema 1 +Options

8536SCG3V06C6X20

Discontinued

Main

Product Type	Starter
Product Range	S
Starter Type	Non reversing

Complementary

Nema Size	1
Rated Current	27 A
Number Of Poles	3P
Maximum Voltage Rating	600 V AC
Phase	3 phase
Type Of Overload	Melting alloy 3
Horsepower Rating	7.5 HP 200 V AC 7.5 HP 230 V AC 10 HP 460 V AC 10 HP 575 V AC
Coil Voltage	440 V AC 50 Hz 480 V AC 60 Hz
Control Circuit Type	Common control circuit
Control Units	Selector switch (ON-OFF)
Auxiliary Contacts	2 NO
Terminal Type	Screw clamp terminals

Environment

Enclosure Type	NEMA 1 painted sheet steel
Certifications	UL Listed NEMA CSA

Ordering and shipping details

Category	21192-8502,36 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
Returnability	No
Country Of Origin	MX

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	6.00 lb(US) (2.722 kg)

Contractual warranty

Warranty	18 months
----------	-----------