

Product data sheet

Specifications

SQUARE D



Non-Reversing Starter Size 1, 3-Pole, Melting Alloy Overload, Nema 1 +Options

8536SCG3V84CF4TX11

Discontinued

Main

| | |
|---------------|---------------|
| Product Type | Starter |
| Product Range | S |
| Starter Type | Non reversing |

Complementary

| | |
|------------------------|--|
| Nema Size | 1 |
| Rated Current | 27 A |
| Number Of Poles | 3P |
| Maximum Voltage Rating | 600 V AC |
| Phase | 3 phase |
| Type Of Overload | Melting alloy 3 |
| Horsepower Rating | 7.5 HP 200 V AC 7.5 HP 230 V AC 10 HP 460 V AC 10 HP 575 V AC |
| Coil Voltage | 120 V AC 60 Hz secondary circuit 208 V AC 60 Hz primary circuit |
| Control Circuit Type | Control circuit transformer |
| Control Units | Selector switch (HAND-OFF-AUTO) |
| Auxiliary Contacts | 1 NO + 1 NC |
| Other Equipment | 2 fuses (primary) |
| Terminal Type | Screw clamp terminals |

Environment

| | |
|----------------|----------------------------|
| Enclosure Type | NEMA 1 painted sheet steel |
| Certifications | CSA NEMA UL Listed |

Ordering and shipping details

| | |
|-------------------|----------------------------------|
| Category | 21192-8502,36 SC,SD(NOT S*R,T,W) |
| Discount Schedule | CP1 |
| Returnability | No |
| Country Of Origin | MX |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

| | |
|------------------------------|--------------------------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Weight | 26.37 lb(US) (11.961 kg) |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|