

# Product data sheet

Specifications

SQUARE D



## Non-Reversing Starter Size 1, 2-Pole, Melting Alloy Overload +Options

8536SCO1V02X21Y342

Discontinued

### Main

Product Type	Starter
Product Range	S
Starter Type	Non reversing

### Complementary

Nema Size	1
Rated Current	27 A
Number Of Poles	2P
Maximum Voltage Rating	600 V AC
Phase	1 phase
Type Of Overload	Melting alloy 1
Horsepower Rating	3 HP 230 V AC 2 HP 115 V AC
Coil Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Control Circuit Type	Common control circuit
Control Units	No control units
Auxiliary Contacts	2 NO + 1 NC
Terminal Type	Screw clamp terminals

### Environment

Enclosure Type	Not rated (open device)
Certifications	UL Listed NEMA CSA

### Ordering and shipping details

Category	21192-8502,36 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
Returnability	No
Country Of Origin	MX

### Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	5.00 lb(US) (2.268 kg)

## Contractual warranty

Warranty	18 months
----------	-----------