

# Product data sheet

Specifications



NEMA motor starter, Type S, nonreversing, Size 1, 27A, 10HP at 460VAC, 5kA SCCR, 3 phase, 3 pole, melting alloy, 480VAC coil, open

8536SCO3V06

Product availability: Stock - Normally stocked in distribution facility

Price\*: 557.00 USD

## Main

Product Type	Motor starter
Product Range	S
Starter Type	Non reversing

## Complementary

Nema Size	1
Rated Current	27 A
Number Of Poles	3P
Maximum Voltage Rating	600 V AC
Phase	3 phase
Type Of Overload	Melting alloy 3
Horsepower Rating	7.5 HP 200 V AC 7.5 HP 230 V AC 10 HP 460 V AC 10 HP 575 V AC
Sccr	Circuit-breaker: 5 kA at 600 V AC Fuse: 5 kA at 600 V AC
Coil Voltage	440 V AC 50 Hz 480 V AC 60 Hz
Control Circuit Type	Common control circuit
Control Units	No control units
Pilot Light	Without pilot light
Auxiliary Contacts	Without
Terminal Type	Screw clamp terminals
Height	6.81 in (172.96 mm)
Width	3.50 in (88.90 mm)
Depth	4.22 in (107.19 mm)

## Environment

Enclosure Type	Not rated (open device)
----------------	-------------------------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Certifications	UL Listed CSA NEMA
----------------	--------------------------

## Ordering and shipping details

Category	US10CP121192
Discount Schedule	0CP1
Gtin	785901864806
Returnability	Yes
Country Of Origin	MX

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.49 in (11.4 cm)
Package 1 Width	5.98 in (15.2 cm)
Package 1 Length	8.11 in (20.6 cm)
Package 1 Weight	4.03 lb(US) (1.83 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)


## Well-being performance

 Pvc Free

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Not compliant
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>

Dimensions Drawings

Approximate Dimensions and Clearance



NEMA SIZE 1 STARTER  
3-Pole Polyphase 600 VAC. 50-60 HZ

Coil Voltage Code (*)	Voltage	
	60 HZ	50 HZ
V01	24	—
V02	120	110
V08	208	—
V03	240	220
V06	480	440
V07	600	550
V99	Specify	Specify

Catalog Number: 8536SCO3(\*)  
Weight: 5 LB  
Wire Size: Power: #14-#8  
Control: #16-#12  
Terminal Torque: 20 LB/IN  
Mounting Hwd. (3) #10 Screws